Maglev | E30214-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Large aluminum extrusions with indirect lighting highlights cut outs in this architectural outlook. Directed outwards toward the cutouts, these sconces are rated for outdoor applications. Select from Black or Architectural Bronze finishes and two sizes of sconce, one of which is scaled for larger faÃ§ade applications.



MEASUREMENTS

DIMENSION	: 6.25" W x 17.75" H x 3.25" Ext
BACK PLATE	: 4.75" W x 16.5" H x 9" HCO
HANGING WEIGHT	: 5.1 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,260 Rated (810 Del.)
BULB	: 1 x 18W LED AC Integrated , 18W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

Architectural Bronze (ABZ)
Black (BK)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com