



Technical Data

Color	Black
Sizes Available	S/M-2XL/3XL
Packaging	Bagged Each
Case Weight (lbs)	0.00
Country of Origin	United States
Certifications	TAA Compliant
Harness Points of Adjustment	5
Harness Style	H
Extended D-Ring	No
Coated	No
Harness Integrated Padding	Yes
Harness Integrated Chair	No
Harness Reflective Webbing	No
Webbing Material	Kevlar®/Nomex®

Miller® Revolution

Arc-Rated Premium Full-Body Harness with Kevlar®/Nomex® DualTech™ Webbing, 5 Points of Adjustment, Back D-Ring, Sub-Pelvic Strap and Quick-Connect Chest & Leg Buckles

- Designed to protect workers from falls caused by electric arc-flash and arc-blast exposure
- Kevlar®/Nomex® DualTech webbing is durable, fire-retardant, and comfortable with 10,000 lb tensile strength
- Webbing offers the durability of FR Kevlar® on the outer side, with softer FR Nomex® on the inside
- PivotLink connection points use a rotary design for mobility and as attachment points for tools and accessories
- Quick-connect buckles with dual-tab release prevent accidental opening and ensure easy donning
- Leather insulators protect against metal hardware contact
- Kevlar® web loop enables metal-less connection with compatible Kevlar lanyards
- Bright red binding identifies arc-rated harnesses easily
- Certified to meet ASTM F887-05, OSHA, ANSI, and CSA requirements
- High load capacity of 400 lbs
- Ideal for utility and maintenance workers operating near energized electrical sources

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
RKNAR-QC/S/MBK	Black	S/M	612230147839		
RKNAR-QC/UBK	Black	L/XL	612230144098		00612230302955
RKNAR-QC/3XLBK	Black	2XL/3XL	612230148942		
RKNAR-QC/4XLBK	Black	4XL	612230240790		