Project / Job Name:

Location:

Fixture Type:

Notes:



**62-3245** - Huntington; 24-Inch LED Vanity; 30 Watt; 3000K-1800K CCT; Polished Nickel Finish; Faux Alabaster Glass

## GENERAL

| | |
|---|---|
| Company | NUVO |
| EA Height | 6.25 |
| EA Width | 5.0 |
| EA Length | 25.38 |
| Mounting Height | 4.38 |
| Mounting Length | 24.0 |
| Mounting Width | 4.38 |
| Bulb Included | Integrated |
| Extends (in) | 4.38 |
| Material | Steel |
| Includes | Screws and Plastic Anchors |
| Status | Active |
| Style | Modern and Contemporary |
| Surge Protection | Built-in surge protection - 1.5KV |
| Total Harmonic Distortion | <45% |
| Top To Outlet | 2.13 |
| Up Down Installation | Universal |
| CCT Selectable | Yes |
| Wattage Selectable | No |
| Collection | Huntington |
| Finish Family | Nickel |
| Amps | 0.290A |
| Lens Finish | Faux Alabaster |
| Lens Material | Acrylic |
| Nominal Length | 24.0 |
| Power Factor | >0.9 |
| Indoor Outdoor | Indoor |
| Product Technology | LED |
| Fluor Equiv | 40W |
| Incandescent Equivalent | 155W |
| Serviceable Battery | No |
| Battery Indicator | No |
| Digital Display | No |

## ELECTRICAL

| | |
|---|---|
| CCT (Kelvin Temp) | 3000K-1800K |
| Dimmable | Yes-Dimmable |
| Hours Rated | 30000 |
| Beam Angle (degree) | 120 |
| Color Temp | Soft White to Warm White |
| CRI | 95+ |
| Dimming Type | Phase Cut (TRIAC) |
| Operating Frequency | 60Hz |
| Operating Temp | -40F to +194F (-40C to +90C) |
| Lumens | 2400L |
| Volts | 120v |
| Watts | 30W |
| Connection | Hardwire |

## PHYSICAL

| | |
|---|---|
| Lamp Base | Integrated |
| Finish | Polished Nickel |
| Housing Color | Polished Nickel |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Fixture Shape | Rectangle |

## ADDITIONAL INFO

| | |
|---|---|
| Warranty | 3-Years |
| Rated For Enclosed Fixture | No |

## PACKAGING

| | |
|---|---|
| UPC | 045923416774 |
| Case Cube | 0.459 |
| Case Height | 6.25 |
| Case Length | 25.38 |
| Case Quantity | 1 |
| Case UPC | 10045923416771 |
| Case Weight | 9.35 |
| Case Width | 5.0 |
| EA Cube | 0.459 |
| EA Height | 6.25 |
| EA Length | 25.38 |
| EA Quantity | 1 |
| EA Weight | 9.35 |
| EA Width | 5.0 |
| Pack Type | Kraft Box |
| Web Height | 4.38 |
| Web Width | 24.0 |

## COMPLIANCE

| | |
|---|---|
| ADA Compliant | No |
| Air Tight | No |
| CA Prop 65 | Lead |
| Dark Sky Rated | No |
| FCC Compliant | Yes |
| IP Rating | IP20 |
| Location Rating | Damp |
| NSF Approved | No |
| ROHS Compliant | Yes |
| Safety Listing | cETLus |
| California Ban | Lawful for sale |
| Energy Star Certified | No |
| Title 20 | Exempt |
| T24/JA8 Compliant | Yes |



© Satco Products, Inc.
All rights reserved 2026