



## Main

Product Type	Load Center Cover
Marketing Trade Name	Homeline
Cover Type	Combination flush/surface cover

## Complementary

Number of Spaces	12
Surface Finish	Baked enamel Gray
Height	19.12 in (485.65 mm)
Width	15.44 in (392.18 mm)
Tightening Torque	Screw 2.3 N.m

## Ordering and shipping details

Category	00183 - HOM LC REPLACEMENT COVERS
Discount Schedule	DE5
GTIN	00785901077503
Nbr. of units in pkg.	1
Package weight(Lbs)	7.09 lb(US) (3.22 kg)
Returnability	Yes
Country of origin	US

## Packing Units

Package 1 Height	1.30 in (3.302 cm)
Package 1 width	15.60 in (39.624 cm)
Package 1 Length	19.40 in (49.276 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

---

Warranty

Lifetime

---