



Exam Black Nitrile Disposable Gloves

Product Code: GWBEN

Gloveworks® Exam Black Nitrile Gloves (GWBEN) are just what you need for both industrial and medical use. Their 7-mil thickness provides strong resistance to punctures, rips, and tears, and protects against chemicals and pathogens. The black color, which looks professional and hides dirt, grease, and grime, has been tested to resist permeation by fentanyl for up to 240 minutes based on the ASTM D6978 standard. Perfect for applications from automotive to jan/san, veterinary to public safety, security to tattoo parlors.

KEY USER BENEFITS:

- Textured firm grip
- Fentanyl tested
- Medical grade - meets AQL 1.5
- Black color allows for identification of light-colored foreign substances

FEATURES:

- Textured
- Powder Free
- Latex Free
- Available Sizes: S-XXL



Automotive



Janitorial



Medical



Paint



Plumbing

CERTIFICATION



Tested for Resistance to Permeation
by Fentanyl as per ASTM D6978



GENERAL DESCRIPTION			
Color	Black	Usage	Single Use
Material	Nitrile	Interior	Powder Free
Grade	Exam	Exterior	Textured
Shape	Ambidextrous	Process	Polymer Coated
Cuff	Beaded	Latex Content	Latex-Free
Type	Non-Sterile	Sizes	S-XXL

PHYSICAL PROPERTIES								
Size		Unit	Small	Medium	Large	X-Large	XX-Large	Standard Method
Weight		±0.2 g	-	6.5	-	-	-	-
Width		±5 mm	85	95	105	115	125	ASTM D412 ASTM D3767
Thickness	Cuff	±1 mil / ±0.02 mm	5 / 0.12	5 / 0.12	5 / 0.12	5 / 0.12	5 / 0.12	
	Palm	±1 mil / ±0.02 mm	6 / 0.14	6 / 0.14	6 / 0.14	6 / 0.14	6 / 0.14	
	Finger	±1 mil / ±0.02 mm	7/ 0.18	7/ 0.18	7/ 0.18	7/ 0.18	7/ 0.18	
Minimum Length		mm	240					
Maximum Powder Content		mg/glove	2					ASTM D6124
Maximum Protein Content		µg/dm²	N/A					ASTM D5712
			Before Aging		After Aging			Standard Method
Minimum Tensile Strength		MPa	14		14			ASTM D412
Minimum Ultimate Elongation		%	500		400			

PRODUCT QUALITY AND REGULATORY COMPLIANCE	
QMS Audit Standards	ISO 9001:2015; ISO 13485:2016
Regulatory and Standard Compliance	California Proposition 65; REACH; FDA 21 CFR 177.2600; FDA 510(k); ASTM D6319, ASTM D6978 (Tested for fentanyl)
AQL Level	1.5

PRODUCT CODE AND PACKAGING					
Size	Small	Medium	Large	X-Large	XX-Large
Product Code	GWBEN42100	GWBEN44100	GWBEN46100	GWBEN48100	GWBEN49100
Box Barcode	 S Box	 M Box	 L Box	 XL Box	 XXL Box
Case Barcode	 S Case	 M Case	 L Case	 XL Case	 XXL Case
Quantity	100 Gloves Per Box, 10 Boxes Per Case				