



North[®] Zone[™]

Type I, Cap Style Hard Hat with HDPE Shell, 4-Point Textile Suspension and Wheel Ratchet Adjustment

- HDPE material
- Patented ratchet suspension with multiple adjustment points
- Rear cradle enhancing retention
- Side slots for attachments
- Reverse donning capable
- ANSI/CSA Certified, Type I, Class E

Technical Data

Color	Orange, Brown, Red, Black, White, Blue, Gray, Dark Blue, Yellow, Hi-Vis Orange, Green, Pink
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	22.38 x 22.50 x 18.50
Case Weight (lbs)	14.99
Country of Origin	Mexico
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Short
Size Adjustment	Wheel Ratchet
Certifications	ANSI/ISEA Z89.1, EN 397, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
N10R110000	Black	OS	883940248776		00883940248783
N10R170000	Blue	OS	883940248851		00883940248868
N10R070000	Brown	OS	883940248691		00883940248707
N10R080000	Dark Blue	OS	883940248714		00883940248721
N10R090000	Gray	OS	883940248738		00883940248745
N10R040000	Green	OS	883940248653		00883940248660
N10R460000	Hi-Vis Orange	OS	883940248912		00883940248929
N10R030000	Orange	OS	883940248639		00883940248646
N10R200000	Pink	OS	883940248875		00883940248882
N10R150000	Red	OS	883940248837		00883940248844
N10R010000	White	OS	883940248592		00883940248608
N10R020000	Yellow	OS	883940248615		00883940248622