SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

S30101 - LED Compact Work Light; 2000 Max Lumens; USB-C Rechargeable; 3.7 Volt; 6pc Tray Pack

GENERAL

Company	SATCO
EA Height	7.5
EA Width	6.25
EA Length	2.0
Material	ABS Plastic /Thermoplastic Rubber (TPR) / Polycarbonate (PC)
Fixture Type	Rechargeable Work
Includes	USB-A to USB-C Charging Cable
Product Notes	Integrated Rechargeable 3.7V Li-ion Battery; Power Bank: 3000mAh; Charge Time: 5HRS
Status	Active
CCT Selectable	No
Wattage Selectable	No
Finish Family	Black
Additional Info	Ships in retail-ready display trays and packaging
Integrated Features	Power Bank; Adjustable Magnetic Base; Hang Hook; Keyhole Mount; Impact Absorbing Housing
Lens Finish	Frost
Lens Material	Polycarbonate (PC)
Lensed	Yes
Portable Light Modes	High, Low, Medium
Product Technology	LED
Serviceable Battery	No
Beam Distance (Ft)	197
Battery Indicator	Yes
Digital Display	No
Drop Impact Rating	3.28 Ft (1M)
Battery Operating Temp	+32F to +104F (0C to +40C)
Light Source Quantity	Single
Power Bank Storage	3000mAh

ELECTRICAL

CCT (Kelvin Temp)	6500K
Dimmable	Yes-Dimmable
Color Temp	Daylight
CRI	80+
Dimming Type	Only dimmable via setting selection, Step Dimming
Operating Temp	+32F to +104F (0C to +40C)
Lumens	2000L/1000L/500L
Volts	3.7V
Max Lumens	2000L
Connection	USB-C Rechargeable
Charge Time	5hr
Battery Chemistry	Lithium-ion (Li-ion)
Replaceable Battery Type	18650
USB Type In	1 USB-C
USB Output Charging Power	(1) 1A 5V
USB Type Out	1 USB-A 1A

PHYSICAL

Finish	Black / Gray / Red
Housing Color	BlackGrayRed
Mounting Procedure	Hang Hook, Magnetic Base, Stand Base

ADDITIONAL INFO

Warranty	1-Year
Installation Notes	Do Not Charge The Product Below 40F Or above 104F; Do Not Exceed 5V DC, 1A Charging
Portable Light Functions	White Light Function

PACKAGING

UPC	045923300028
Case Cube	1.1456
Case Height	9.84
Case Length	13.27
Case Quantity	12
Case UPC	10045923300025
Case Weight	14.68
Case Width	15.16
EA Cube	0.0543
EA Height	7.5
EA Length	2.0
EA Quantity	1
EA Weight	0.89
EA Width	6.25
Inner Cube	0.4155
Inner Height	8.74
Inner Length	12.28
Inner Quantity	6
Inner UPC	20045923300022
Inner Weight	6.6
Inner Width	6.69
Pack Type	Color Box
Web Height	1.69
Web Length	5.11
Web Width	4.33

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IPX4
ROHS Compliant	Yes
Energy Star Certified	No
T24/JA8 Compliant	No
Performance Standards	ANSI PLATO FL1

© Satco Products, Inc.
All rights reserved 2026