



Project / Job Name: _____

Location: _____

Fixture Type: _____

Notes: _____

JH5070 - Orb LED Track Head; 12 Watt;
3000K/4000K/5000K CCT Selectable; 24 Degree Beam
Angle; J-Style; White; 120 Volt



GENERAL

Company	SATCO
EA Height	1.73
EA Width	5.4
EA Length	7.87
Bulb Included	Integrated
Diameter	4.7
Dimmable Text	Forward Phase; Linear Dimming
Material	Aluminum
Fixture Type	Track Head
Status	Active
Style	Contemporary
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	<40%
Track Head Style	Circle
Up Down Installation	Universal
CCT Selectable	Yes
Wattage Selectable	No
Collection	Orb
Finish Family	White
Amps	0.120A
Lens Material	Poly methyl methacrylate (PMMA)
Lensed	Yes
Power Factor	0.9
SDS Class	LED_Fixture
Sloped Ceiling Compatible	Yes
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	75W

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	24
Color Temp	Soft White to Natural Light
CRI	90+
Dimming Type	Linear Dimming, Phase cut
Operating Frequency	60Hz
Operating Temp	-20C (-4F) to +40C (+104F)
Lumens	1020L
Volts	120v
Watts	12W

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO

Warranty	3-Years
----------	---------

PACKAGING

UPC	045923412622
Case Cube	0.6517
Case Height	8.66
Case Length	11.61
Case Quantity	12
Case UPC	10045923412629
Case Weight	12.05
Case Width	11.2
EA Cube	0.0425
EA Height	1.73
EA Length	7.87
EA Quantity	1
EA Weight	0.92
EA Width	5.4
Pack Type	Kraft Box
Web Height	7.13
Web Length	5.63
Web Width	1.3

COMPLIANCE

CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Dry
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Title 20	Exempt
T24 Compliant	Yes