



P65

Technical Data

Color	Green
Sizes Available	S-5XL
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	14.96 x 11.81 x 12.20
Case Weight (lbs)	35.27
Country of Origin	China
Fabric	PVC, Nylon, Nylon, Nylon, Nylon
Thickness	0.42 mm
Hood	Attached
Closure	Zipper
Construction	Reinforced Wear Points, Double Storm Flap

Care Instructions



Do Not Wash

PIP® ChemFR™

Treated PVC Jacket with Hood - 0.42 mm

- Special PVC layered material provides protection against various liquid splashes and incidental contact
- High strength nylon for increased durability
- Seams are welded to enhance protection against chemical permeation
- Reinforced elbows provide added durability
- Oversized storm flap front for additional protection
- Treated to provide limited flammability and is self-extinguishing (ASTM D6413 test method)
- ⚠ **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Road Work
- Municipal
- Shipyards
- Railyard
- Agriculture
- Plant Maintenance
- Not designed for use in an ARC flash or flash fire application

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
205-420JH/S	Green	S	616314193590	01616314193599	02616314193598
205-420JH/M	Green	M	616314193606	01616314193605	02616314193604
205-420JH/L	Green	L	616314193613	01616314193612	02616314193611
205-420JH/XL	Green	XL	616314193620	01616314193629	02616314193628
205-420JH/2X	Green	2XL	616314193637	01616314193636	02616314193635
205-420JH/3X	Green	3XL	616314193644	01616314193643	02616314193642
205-420JH/4X	Green	4XL	616314193651	01616314193650	02616314193659
205-420JH/5X	Green	5XL	616314193668	01616314193667	02616314193666