

PAINTED NO. 2

MDS351-PN/SSG

Tried-and-true, Painted No. 2 has an effortless look that is the result of careful consideration. A relaxed form with timeless style, it is now available in even more beautiful finish options that give it a renewed sense of freshness. Its classic heritage feel is reflected across all formats, including a sconce and pendant in three sizes.

FINISHES

POLISHED NICKEL w/ SOFT STUDIO GREEN

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 9.25"

Width/Diameter: 9.5"

Minimum Height: 12.75"

Maximum Height: 65"

Canopy/Backplate: 5.25"

Hanging Type: 54" Chain

Product Weight: 4.18lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

Shade

Shade 1: Metal

Shade 1 Top Width: 3.5"

Shade 1 Bottom L/W: 0" / 9.5"

Shade 1 Height: 4.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: T10-5.5

Max Wattage: 8

Bulb Quantity: 1

Bulb Included: No

Wire Length: 120"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 13" x 13" x 13"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: CN

