



Dynamic™ Piper™ Passive Ear Muffs with Adjustable Headband - NRR 24

- Value high tensile strength plastic banded style ear muff
- Low profile design increases stability and reduces risk of snagging in confined spaces
- Smooth slide size adjustment for improved fit and comfort
- Dielectric / non-conductive
- Easy to replace snap-in replacement ear cushions

Applications

- Airports
- Construction Applications
- Manufacturing
- Oil and Gas
- Transportation

Technical Data

Color	Orange
Sizes Available	OS
Packaging	Bagged Each
Packed	20 Pair/Case
Case Dimensions (in)	22.99 x 16.38 x 9.25
Case Weight (lbs)	13.23
Country of Origin	Taiwan
Hearing Style	Headband
Protection Type	Passive
Construction	Dielectric, Snap-In Cushions
Certifications	TAA Compliant
Product Circularity	Reusable / Launderable

Performance Data

NRR Rating (ANSI S3.19-1974)	24
SLC 80 Class	Class

Care Instructions

Routinely wash with mild soap and water. Allow cushions to air dry.

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-16

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
263-NP110	Orange	OS	616314275265	10616314370493	20616314275269