# **Celine** | E24432-112NAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







## PRODUCT DESCRIPTION

### MEASUREMENTS

| | |
|---|---|
| DIMENSION | : 5.5" L x 5.5" W x 24" H x 2.25" Ext |
| BACK PLATE | : 5.5" W x 20.25" H x 12" HCO |
| HANGING WEIGHT | : 5.95 lb |

### LAMPING

| | |
|---|---|
| INPUT VOLTAGE | : 120-277V |
| LUMENS | : 1,430 Rated (920 Del.) |
| BULB | : 1 x 20.5W LED DC Integrated , 20W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : Triac, ELV |
| CRI | : 90 CRI |
| COLOR_TEMP | : 27-30-35-40-50K |
| LIGHTING_DIRECTION | : Up/Down |

### FINISHES OPTION

- Black (BK)
- Natural Aged Brass (NAB)
- Satin Nickel (SN)

### GLASS

White Spiral 112

### MATERIAL

Aluminum, Glass

### RATINGS

cETLus
Wet Location
ADA

### ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com