PRODUCT INFORMATION PACKET

Model No: OCA3074
Catalog No: OCA3074
Condenser Fan Motor, 3/4 HP, 3 Ph, 60 Hz, 208-230/460 V, 56Y Frame, ODP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
Â©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	**3/4 Hp**	Output KW	**0.56 kW**
Frequency	**60 Hz**	Voltage	**208-230/460 V**
Current	**2.5/1.25 A**	Speed	**1725 rpm**
Service Factor	**1.15**	Phase	**3**
Duty	**Continuous**	Insulation Class	**B**
Frame	**56Y**	Enclosure	**Open Drip Proof**
Thermal Protection	**No Protection**	Ambient Temperature	**40 °C**
UL	**No**	CSA	**N**

Technical Specifications

Rotation	**Reversible**	Mounting	**Rigid Base**
Drive End Bearing	**Ball**	Shaft Extension	**5/8 X 1.9 in**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:02/16/2023