



TEGERA® 866

Learn more

BLACK, MULTI-PACKED STANDARD PU GLOVE

Multi-packed (6 pairs in 1 pack) synthetic glove in dirt masking black color for extended product life. 13 gg knitted, PU palm-dipped with smooth finish for good grip on dry and moist surfaces. Seamless design for better fit, suitable for precision work in versatile areas.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Good grip
- Comfortable

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly, Assembly, Inspection work, Installation work, Engineering, Machine driving, Warehouse work

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Electrical equipment manufacturing, Electricity and gas supply, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Transport equipment manufacturing, Transportation and logistics

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL Polyester
LENGTH 220-260 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR Black
QUANTITY PER PACK 6 Pairs
PACKS PER: BUNDLE/CARTON Not sold in bundle/20
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Polyester
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018
3121X

ANSI 3 ABR

SIZE		ARTICLE NUMBER	EAN
6	XS	866-6	7392626070981
7	S	866-7	7392626063471
8	M	866-8	7392626063488
9	L	866-9	7392626063495
10	XL	866-10	7392626063501
11	XXL	866-11	7392626063518

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.