
Studio I

This classic nautical look is especially popular in traditional design settings. Its exquisite detailing and functional black baffle make it an important design element as well as an effective luminaire. The MR16 version is manufactured with an integral magnetic transformer which is especially useful in rough-duty applications.



Catalog #	Finish	Lamp
T338WH	White	12V, 50W max. MR16

Dimensions




Integral 12V
Magnetic Transformer



Catalog #	Finish	Lamp
T393WH	White	50W max. R20/ 50W max. PAR20


Dimensions





Catalog #	Finish	Lamp
T395WH	White	75W max. BR30 or 75W max. PAR30L


Dimensions





Catalog #	Finish	Lamp
T397WH	White	150W max. PAR38 or 120W max. BR40

Dimensions



Accessories

For Fixtures:	*T338***	*T393*	*T395*	*T397*
Accessory Holder	**T570BL**	**T560BL**	**T570BL**	**T580BL**
Color Filters	**T571-6**	**T561-6***	**T571-6***	**T581-6***
Color Filters	**T551-5**	**–**	**–**	**–**
Dichroic Filters	**T5501-18**	**T5601-18***	**T5701-18***	**–**
Dichroic Filters	**T5701-18**	**–**	**–**	**–**
Diffusion Lens	**T5520**	**T5620***	**T5720***	**–**
Uniformity Lens	**T5521**	**T5621***	**T5721***	**–**
UV Filter	**T5522**	**T5622***	**T5722***	**–**
Prismatic Spread Lens	**T557**	**T5677***	**T5777***	**–**
Linear Spread Lens	**T559**	**T5678***	**T5778***	**–**
Hexcell Louver	**T5559BL**	**–**	**–**	**–**
Cube Cell Louver	**T579BL**	**T569BL***	**T579BL***	**T589BL***
White Barn Doors	**–**	**–**	**–**	**T73WH**
Black Barn Doors	**T72BL**	**T71BL**	**T72BL**	**T73BL**

* Filters, lenses and louver require accessory holder for installation.

** T338 can accept one 1 3/4" filter, lens or louver in place of clear glass supplied with MR16 fixtures; in addition, it can also accept one 4 11/16" filter, lens or louver when combined with accessory holder or barn doors.