



**MCR
SAFETY**

22 Goggles Series Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety's 22 Series Goggles provide a wide, unobstructed field of vision and can be worn with most half-mask respirators. The 2235R features an Indirect Vented transparent protective PVC body that permits a comfortable fit over prescription eyewear while protecting against impact. This goggle has a UV-AF® Anti-Fog coated lens that is Eco-friendly and UV cured, providing 3 times greater Anti-Fog performance than generic Anti-Fog safety goggles. The adjustable rubber strap is comfortable, flexible and fits a variety of individuals. Also Available in ventless or perforated styles. Choose the best safety goggles, choose MCR Safety!

California Prop 65 Warning: This product contains chemicals known to the State of California to cause cancer, birth defects or other reproductive harm.



FEATURES:

- PVC body permits a comfortable fit over prescription eyewear
- Options available to protect against impact, small particles and debris
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays
- UV-AF® Anti-Fog Coating
- Adjustable rubber strap will not soak liquids and is latex free
- Indirect vented

TECHNICAL DATA FOR: 2235R

Series	22	ANSI Z87+	Yes
Category	Goggles	ANSI D3 SPLASH	Yes
Goggle Type	Indirect Vented	ANSI D4 DUST	Yes
Dielectric	Yes	Packaging	White Inner Box
Anti-Fog	Yes		
Scratch Resistant	Yes		
Frame Material	PVC		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved



MCR
SAFETY

22 Goggles Series Specification Sheet

Case Pack	144	Case Weight	34.344 lb.
Case Dimensions	16.929 x 16.929 x 25.197	Made In	Taiwan

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Goggle Type:
2120	Clear	Duramass Hard Coat	Yes	90	Clear	Direct Vented / Perforated
2220	Clear	Duramass Hard Coat	Yes	90	Clear	Direct Vented / Perforated
2220R	Clear	Duramass Hard Coat	Yes	90	Clear	Direct Vented / Perforated
2225	Clear	UV-AF Anti-Fog	Yes	90	Clear	Direct Vented / Perforated
2225R	Clear	UV-AF Anti-Fog	Yes	90	Clear	Direct Vented / Perforated
2225RB	Clear	UV-AF Anti-Fog	Yes	90	Clear	Direct Vented / Perforated
2230	Clear	Duramass Hard Coat	Yes	90	Clear	Indirect Vented
2230R	Clear	Duramass Hard Coat	Yes	90	Clear	Indirect Vented
2230RB	Clear	Duramass Hard Coat	Yes	90	Clear	Indirect Vented
2235	Clear	UV-AF Anti-Fog	Yes	90	Clear	Indirect Vented
2235R	Clear	UV-AF Anti-Fog	Yes	90	Clear	Indirect Vented
2235RB	Clear	UV-AF Anti-Fog	Yes	90	Clear	Indirect Vented
2237	Clear	UV-AF Anti-Fog	Yes	90	Clear	Ventless
2237R	Clear	UV-AF Anti-Fog	Yes	90	Clear	Ventless

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved