



jalas® GRIP 3780 FOODS

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2022 S2, HRO, FO

Learn more

FOR HIGH HYGIENIC REQUIREMENT AREAS

This boot provides the highest protection in high hygienic requirement areas. It is extra comfortable with excellent grip and perfect fit. Water repellant thanks to upper material in PU-coated leather. Toe cap in aluminium. Oil resistant and heat resistant outsole. By purchasing this product, you are supporting Leather Working Group certified tanneries.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- Oil-resistant outsole
- Anti-static properties
- Padded boot shaft
- Ventilating insole
- Water repellent
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)
- Heat-resistant outsole

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Toe injuries, Antistatic

PRIMARY ENVIRONMENTS OF USE
Outdoors, Indoors, Harsh environments

PRIMARY AREAS OF USE
Foodstuff handling, Food handling

PRIMARY INDUSTRIES OF USE
Food and beverage processing

SPECIFICATION
TYPE Safety footwear, Boots
CATEGORY Cat. II
FITTING Regular
COLLECTION Grip
UPPER MATERIAL PU-coated leather
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester, polyamide
INSOLE JALAS 8103 FX2 Pro-X
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
COLOUR Black
NET WEIGHT, (SIZE 42) 1.36 kg

COMPLIANCE
CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

EN ISO 20345:2022
S2, HRO, FO

FEATURES
- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Heat-resistant outsole
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	3780-36	6408487436277
37	4	5	6	3780-37	6408487436284
38	5	5.5	6.5	3780-38	6408487436291
39	6	6.5	7.5	3780-39	6408487436307
40	6.5	7.5	8.5	3780-40	6408487436314
41	7	8	9	3780-41	6408487436321
42	8	9	10	3780-42	6408487436338
43	9	9.5	11	3780-43	6408487436345
44	10	10.5	11.5	3780-44	6408487436352
46	11	12	13	3780-46	6408487436376
47	12	13	14	3780-47	6408487436383

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.