



MOTICAM Series

MOTICAM BTI8





MOTICAM Series - Tablet Cameras

MOTICAM BT18

Camera Specifications

Sensor type	CMOS
Sensor size	1/3"
Live resolution	1920x1080, 1280x720 (display resolution)
Image capture resolution	4.0MP
Video capture resolution	720P (HD)
Data transfer	Wi-Fi (2.4 or 5 GHz) and Ethernet (RJ45)
Pixel size	2.0µm x 2.0µm
Lens mount	C-Mount
Tablet bracket holder	For tablets from 7" to 10"

Tablet Specifications

Size	209x126x9.9mm
System	Android 5.1
Pre-installed App	MotiConnect
Language	Multi-Language
CPU	1.3GHz Quad core
RAM	1GB DDR3
NAND FLASH	8GB
Display	8" (IPS) 16:10 Ratio
Ports	MicroSD/MMC/TF Card (Support up 64 GB), 3.5mm Audio, USB-C (USB OTG and Charging)
Support display format	MPEG-1/2 (DAT, MPG, VOB, TS), MPEG-4, H.263 (3GP, MOV, MP4), H.264 (AVI, MKV, MP4, MOV, 3GP), RM, RMVB, FLV, WEBM
Support audio format	MP3, WMA, MP2, OGG, AAC, M4A, OGA, FLAC, APE, MP1, WAV
Picture format	JPEG, GIF, BMP, PNG
Camera	Front (VGA) + Rear (2M Pixels)
Package includes	USB Cable, Motic 4-dot calibration slide, universal power supply 100V-240V (CE)