
Alumilux Landscape | E41350-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

Low voltage garden lights consisting of classic shaped shades to brighten your outdoor space. Choose from various lighting elements that pair with matching poles. In-ground stakes or bolt down installation mounting options are provided. Extension rods in 8-inch increments sold separately.



MEASUREMENTS

DIMENSION	: 3.5" W x 13.75" H
HANGING WEIGHT	: 1.93 lb

LAMPING

LUMENS	: 230 Rated
BULB	: 1 x 5W LED 12V MR16 , 5W Total
BULB INCLUDED	: (Included)
DIMMABLE	: N
CRI	: 80+ CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Black (BK)
- Bronze (BZ)
- Satin Aluminum (SA)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com