

# QO260CP

Mini circuit breaker, QO, 60A, 2 pole,  
120/240VAC, 10kA, plug in mount, consumer  
pack



## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	60 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Type of Packing	Consumer packaging

## Complementary

Interrupt Rating	10 KA 120/240 V AC 50/60 Hz 10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 8...AWG 2 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m) 0.02...0.04 in <sup>2</sup> (10...25 mm <sup>2</sup> ) (AWG 8...AWG 2)
Height	3.11 in (79 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.55 lb(US) (0.249 kg)

## Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details


Category	01341-QO 2 POLE BULK BRKRS15-60A
Discount Schedule	CPQ
GTIN	047569838064
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	3.10 in (7.874 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	8.80 oz (249.476 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1800
Package 2 Height	40.00 in (101.6 cm)

Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1098.00 lb(US) (498.044 kg)
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Height	3.20 in (8.128 cm)
Package 3 Width	3.10 in (7.874 cm)
Package 3 Length	7.70 in (19.558 cm)
Package 3 Weight	3.00 lb(US) (1.361 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Halogen content performance	Halogen free product