



Project / Job Name:

Location:

Fixture Type:

Notes:

**S21921** - 12 Watt; 36-Inch; T8 LED; 3K/35K/4K/5K/65K CCT; G13 Base; Type B; Frost Finish; Non-Dim; 120-347 Volt



#### GENERAL

|                           |                                 |
|---------------------------|---------------------------------|
| Company                   | SATCO                           |
| EA Height                 | 1.1                             |
| EA Width                  | 1.1                             |
| EA Length                 | 35.78                           |
| Lamp Ballast Type AB      | Type B                          |
| Material                  | Glass / Polycarbonate (PC)      |
| Fixture Type              | Miniature                       |
| Status                    | Active                          |
| Surge Protection          | Built-in surge protection - 1KV |
| Total Harmonic Distortion | <25%                            |
| CCT Selectable            | Yes                             |
| Wattage Selectable        | No                              |
| Finish Family             | White                           |
| Amps                      | 0.100-0.030A                    |
| Nominal Length            | 36.0                            |
| Operating Position        | Universal                       |
| Power Factor              | >0.9                            |
| SDS Class                 | LED_Lamp                        |
| Indoor Outdoor            | Indoor                          |
| Product Technology        | LED                             |
| Fluor Equiv               | 21W/25W                         |

#### ELECTRICAL

|                     |                               |
|---------------------|-------------------------------|
| CCT (Kelvin Temp)   | 3000K/3500K/4000K/5000K/6500K |
| Dimmable            | Non-Dimmable                  |
| Hours Rated         | 50000                         |
| Beam Angle (degree) | 210                           |
| Color Temp          | Soft White to Natural Light   |
| CRI                 | 80+                           |
| Operating Frequency | 50/60Hz                       |
| Operating Temp      | -4F to +113F (-20C to +45C)   |
| Lumens              | 1600L                         |
| Volts               | 120V-347V                     |
| Watts               | 12W                           |

#### PHYSICAL

|           |               |
|-----------|---------------|
| Lamp Base | Medium Bi Pin |
| Finish    | Frost         |
| ANSI Base | G13           |
| Lamp Type | T8            |
| MOD Lamps | 1.0           |
| MOL       | 35.73         |

#### ADDITIONAL INFO

|                            |         |
|----------------------------|---------|
| Warranty                   | 5-Years |
| Rated For Enclosed Fixture | No      |

#### FEATURES

|              |    |
|--------------|----|
| Flicker Free | No |
|--------------|----|

#### PACKAGING

|               |                |
|---------------|----------------|
| UPC           | 045923414428   |
| Case Cube     | 0.7151         |
| Case Height   | 5.87           |
| Case Length   | 36.61          |
| Case Quantity | 25             |
| Case UPC      | 10045923414425 |
| Case Weight   | 10.71          |
| Case Width    | 5.75           |
| EA Cube       | 0.0251         |
| EA Height     | 1.1            |
| EA Length     | 35.78          |
| EA Quantity   | 1              |
| EA Weight     | 0.41           |
| EA Width      | 1.1            |
| Pack Type     | Sleeve         |
| Web Length    | 35.73          |
| Web Width     | 1.0            |

#### COMPLIANCE

|                   |                 |
|-------------------|-----------------|
| Air Tight         | No              |
| CA Prop 65        | Lead            |
| Dark Sky Rated    | No              |
| DLC ID            | S-W03DYP        |
| FCC Compliant     | Yes             |
| IP Rating         | IP20            |
| Location Rating   | Damp            |
| NSF Approved      | Yes             |
| ROHS Compliant    | Yes             |
| Safety Listing    | cULus - Listed  |
| California Ban    | Lawful for sale |
| DLC Approved      | Yes             |
| Title 20          | Exempt          |
| T24/JA8 Compliant | No              |