
SUNCOURT®


CENTRAX® IN-LINE CENTRIFUGAL FAN

6" CENTRAX® IN-LINE CENTRIFUGAL FAN™

ENGINEERED & ASSEMBLED IN USA


N.T.S.





Mounting Hardware:
(4) #8 x 1" Self tapping screws
(4) #6 X 1/2" Machine screws
(4) Hex nuts, (4) #6 Lock washers
(4) Rubber washers
(2) Fan mounting brackets, (2) Cable ties
(6) #6 Screws for securing duct connection

MODEL: TF106



Model #: TF106

Centrax® 6" In-Line Centrifugal Fan

350 Free Air CFM, 140 Running Watts

1.14 Amps, 120 VAC, 60 Hz

Class B or better external rotor motor

Thermally protected auto reset

Ball bearing balanced ABS backward inclined impeller

MET® Listed to UL & CSA Standards for USA & Canada

5 Year Limited Warranty

6" Diameter

PERFORMANCE:

CFM	Watts	Amps	Volts	Hz	dBA	Sones	Weight
350	140	1.16	120	60	59	6.4	6.14lbs

CUSTOMS TARRIFF CLASSIFICATION:

HS Code	Country of Origin
8414596060	USA

PACKAGING METRICS:

	UPC / SCC	WIDTH (in)	HEIGHT (in)	DEPTH (in)	WEIGHT (lbs)
Unit:	066028031068	12.5	12.5	12.5	10
Master Case (1qty):	40066028031066	12.5	12.5	12.5	10

MODEL: TF106