



## FS281

### PRO Full Body Harness: 3D, MB Chest/Legs

#### FEATURES:

- Fixed dorsal D-ring
- Integrated SRL channel
- Side positioning D-rings
- Mating buckle chest
- Friction buckle torso adjusters
- Mating buckle legs
- Shoulder pad

#### FALL ARREST POINT(S):

- 1 Dorsal D-ring
- 1 Integrated SRL channel

#### ITEM WEIGHT:

- 4.5 lbs. (2.0 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.11-2021
OSHA	1926.502, 1910.140

SIZE(S)	
FS281-XS	X-Small
FS281-S/M	Small / Medium
FS281-L/XL	Large / X-Large
FS281-2X	2X
FS281-3X	3X

COMPONENT	MATERIAL SPECIFICATION
Webbing	Polyester
D-ring(s)	Zinc-plated steel
Adjuster buckles	Zinc-plated steel
Chest connection	Zinc-plated steel
Leg connection	Zinc-plated steel
Pad	Polyester mesh; EVA
SRL channel	HDPE