

KEN

B3412-VGL

The mobile-inspired Ken family channels kinetic energy with natural materials and curved silhouettes. Each laminated coconut fiber shade wraps around a light source, highlighting the organic texture of the airy, sculptural forms. A Vintage Gold Leaf frame introduces a note of polish. Available as a 1-light sconce and a 6-light chandelier.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 12"

Width/Diameter: 5"

Canopy/Backplate: 4.75"

Product Weight: 3.3lb

Extension: 5.5"

Top to Center: 6"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Coconut Fiber

Shade 1 Top Width: 5"

Shade 1 Bottom L/W: 0" / 3"

Shade 1 Height: 12"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 14" x 8" x 14"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: PH

