


PRODUCT DESCRIPTION

Pullman offers effortless adjustability in architectural accent lighting. A sleek retractable arm glides from a 90 degree wall position to a full downward aim with no visible hardware. The precision mechanism allows seamless repositioning for both task and ambient light while preserving a clean silhouette. A slightly recessed LED GU10 lamp in a beveled trim reduces glare and simplifies maintenance. Finished in Natural Aged Brass, Satin Nickel, or Matte Black, Pullman is both functional and beautifully refined.



MEASUREMENTS

DIMENSION	: 5" L x 5" W x 7" H
CANOPY	: 5" W x 0.25" H x 5" L
HANGING WEIGHT	: 1.38 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 700 Rated (600 Del.)
BULB	: 1 x 7W LED LED , 7W Total
BULB INCLUDED	: (Included)
DIMMABLE	: TriacÂ orÂ ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Black (BK)
Natural Aged Brass (NAB)
Satin Nickel (SN)

MATERIAL

Aluminium, Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com