

SHAVANI

HL1115201-AGB/CHD

The elongated silhouette of the Shavani lamp is traced with unique detailing. A textural vertical stripe runs the length of the statuesque base, reminiscent of a braid or whipstitch detail. Topped with a generously proportioned off-white linen shade, the creamy Honeydew glaze gives this lamp an earthy sense of comfort. Aged Brass hardware completes Shavani on a classic note.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

AGED BRASS w/ Ceramic Honeydew
Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 26.5"
Width/Diameter: 14"
Canopy/Backplate: 4.75"
Product Weight: 10lb
Canopy/Backplate Shape: Oval
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Textile
Shade 1 Finish: Off White Linen
Shade 1 Top Width: 13"
Shade 1 Bottom L/W: 0" / 14"
Shade 1 Height: 12.5"

ELECTRICAL



Bulb 1

Bulb Included: No
Socket: E26 Medium Base
Bulb Type: A19
Max Wattage: 15
Bulb Quantity: 1
Wire Length: 96"
Cord Type: SPT-2 SILVER
Switch Type: ON/OFF SWITCH ON SOCKET
Gem Box Required (2"x3"): No
Dark Sky: No

SHIPPING

Carton 1: 19" x 19" x 24"
Carton 1 Weight: 19lb
Shipping Method: Ground
Country of Origin: VN

