



NOVAX®

Class 0 Rubber Insulating Glove with Straight Cuff - 14"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meets ANSI/ASTM D120 standard.

Technical Data

Color	Red
Sizes Available	7-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 19.80
Case Weight (lbs)	13.98
Country of Origin	Malaysia
Length	14"
Cuff	Straight
Certifications	ASTM D120, Silicone Free

Performance Data

Electrical Class	Class 0
------------------	---------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
153-0-14/7	Red	7	616314737107	10616314737104	20616314737101
153-0-14/8	Red	8	616314737145	10616314737142	20616314737149
153-0-14/8.5	Red	8.5	616314737787	10616314737784	20616314737781
153-0-14/9	Red	9	616314737183	10616314737180	20616314737187
153-0-14/9.5	Red	9.5	616314737824	10616314737821	20616314737828
153-0-14/10	Red	10	616314737220	10616314737227	20616314737224
153-0-14/10.5	Red	10.5	616314737862	10616314737869	20616314737866
153-0-14/11	Red	11	616314737268	10616314737265	20616314737262
153-0-14/11.5	Red	11.5	616314737909	10616314737906	20616314737903
153-0-14/12	Red	12	616314737305	10616314737302	20616314737309