

RONAN

B5830-TBZH

Adapting a modern, tapered racetrack design to an exterior sconce, Ronan is an ellipse of style and substance. The elongated, rounded shape is accented by a thin, raised centerline, revealing a warm coppery undertone beneath the Textured Bronze finish. The metal silhouette shields visibility of the canopy and LED strip, creating a warm wall wash that illuminates the dark nights.

FINISHES

TEXTURED BRONZE W/ HL

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 30"

Width/Diameter: 6"

Canopy/Backplate: 4.75"

Product Weight: 3.52lb

Extension: 3.5"

Top to Center: 15"

Canopy/Backplate Shape: Square

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

Shade 1: Acrylic

Shade 1 Finish: White

Shade 1 Top Length: 27.25"

Shade 1 Top Width: 3.25"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 21

Bulb Quantity: 1

Bulb Included: Yes

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: ELV, TRIAC

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 3000k

Lumens: 700

Title 24: No

Field Serviceable: No

SHIPPING

Carton 1: 32" x 10" x 6"

Carton 1 Weight: 6lb

Shipping Method: Ground

Country of Origin: CN

