

RALSTON

PTL1429-PBR

The Ralston lamp expresses modern simplicity through a rhythmic composition. Cylindrical and spherical shapes are paired with a simple white linen drum shade that fosters geometric continuity. The stacked solid mango wood base is finished in a rich tobacco stain that accentuates the textural grain. A touch of Patina Brass at the neck lends a timeless accent.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 28.25"

Width/Diameter: 17.5"

Canopy/Backplate: 5"

Product Weight: 7.72lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: White Linen

Shade 1 Top Width: 17"

Shade 1 Bottom L/W: 0" / 17.5"

Shade 1 Height: 11.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 96"

Cord Type: SPT-2 BLACK FABRIC

Switch Type: ON/OFF SWITCH ON SOCKET

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 7" x 7" x 24"

Carton 1 Weight: 23lb

Shipping Method: Truck Only

Country of Origin: IN

