



TEGERA® 43001

Learn more

PU PALM DIPPED, GOOD GRIP

Our most popular cut resistant glove (level B) for versatile applications. A combination of high comfort, flexibility, and medium cut protection thanks to the design and CRF® Technology. Breathable back and grey PU coating on palm with smooth finish provides a good grip on dry to slight moist surfaces.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Comfortable

FUNCTIONS

- Washable in 40° C

CRF®

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Scratches, lacerations

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments

PRIMARY AREAS OF USE

Fine assembly, Assembly, Inspection work, Machine operating, Building and construction, Carpentry, Painting, Installation work, Engineering, Transport work, Warehouse work, Airport work

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Transport equipment manufacturing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Cut resistant gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL CRF® Technology, HPPE, Nylon, Spandex
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level B
CUT RESISTANCE (EN ISO 13997) TDM: 7.9 N
INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Elastane, Nylon
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 4X42B

ANSI/ISEA 105-2024 A2 6 3

FEATURES

Cut protection

40° Washable 40°C

SIZE		ARTICLE NUMBER	EAN
5	XXS	43001-5	7340118329109
6	XS	43001-6	7340118320137
7	S	43001-7	7340118320144
8	M	43001-8	7340118320151
9	L	43001-9	7340118320168
10	XL	43001-10	7340118320113
11	XXL	43001-11	7340118320120

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.