



Project / Job Name:

Location:

Fixture Type:

Notes:

S19911MX - 15 Watt; 48-Inch T8 LED; G13 Base; 5000K CCT; Type B; Frost Finish; 120-277 Volt



GENERAL

Company	SATCO
EA Height	1.1
EA Width	1.1
EA Length	47.78
Lamp Ballast Type AB	Type B
Material	Glass / Polycarbonate (PC)
Fixture Type	Miniature
Status	Active
Surge Protection	Built-in surge protection - 1KV
Total Harmonic Distortion	<25%
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Amps	0.141-0.053A
Nominal Length	48.0
Operating Position	Universal
Power Factor	>0.9
SDS Class	LED_Lamp
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	25W/28W/30W/32W

ELECTRICAL

CCT (Kelvin Temp)	5000K
Dimmable	Non-Dimmable
Hours Rated	50000
Beam Angle (degree)	210
Color Temp	Natural Light
CRI	80+
Operating Frequency	50/60Hz
Operating Temp	-4F to +113F (-20C to +45C)
Lumens	2200L
Volts	120V-277V
Watts	15W

PHYSICAL

Lamp Base	Medium Bi Pin
Finish	Frost
ANSI Base	G13
Lamp Type	T8
MOD Lamps	1.0
MOL	47.75

ADDITIONAL INFO

Warranty	5-Years
Rated For Enclosed Fixture	No

FEATURES

Flicker Free	No
--------------	----

PACKAGING

UPC	045923414565
Case Cube	0.9909
Case Height	5.87
Case Length	48.78
Case Quantity	25
Case UPC	10045923414562
Case Weight	13.6
Case Width	5.98
EA Cube	0.0335
EA Height	1.1
EA Length	47.78
EA Quantity	1
EA Weight	0.49
EA Width	1.1
Web Length	47.75
Web Width	1.0

COMPLIANCE

Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
DLC ID	S-C7N325
FCC Compliant	Yes
IP Rating	IP20
Location Rating	Damp
NSF Approved	Yes
ROHS Compliant	Yes
Safety Listing	cRUus - Recognized Component, cUL - Certified, cUL - Classified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24/JA8 Compliant	No