



KRUD KUTTER® ADHESIVE REMOVER

DESCRIPTION AND USES

Krud Kutter® Adhesive Remover is an effective alternative to hazardous, solvent-based products. This ready-to-use spray removes most glues and adhesives, carpet seam sealer, and mastic without unpleasant odors. Easy to use--just spray on and scrape off to remove leftover stickiness from tags, stickers or tape. Also ideal for removing adhesive remaining after removal of flooring such as tile, carpet, linoleum, laminate, wood or vinyl.

PRODUCT FEATURES

- Water-based, biodegradable formula
- Lifts off most glues, adhesives and mastics
- Contains no inorganic phosphates or environmentally harmful surfactants
- Just spray on and scrape off

PRODUCTS

SKU	DESCRIPTION
336247	8 oz. Trigger Sprayer
394801	24 oz. Trigger Sprayer
AR324	32 oz. Trigger Sprayer
AR014	1 Gallon Bottle
AR05	5 Gallon Pail
AR55	55 Gallon Drum

PRODUCT APPLICATION

DIRECTIONS

Always test on an inconspicuous area first.

1. Saturate surface by applying a liberal amount directly onto the adhesive. Allow time for the remover to work; most adhesives will be loosened in 15-30 minutes.

2. Test scrape a small area to see if adhesive is ready for removal. Scrape away softened adhesive with a wide putty knife or scraper. Multiple coats or stubborn spots may require repeat application.

3. For final clean-up, apply once more to the surface and wipe away any remaining adhesive with a clean cloth.

If used prior to flooring installation, allow surface to dry for at least 1 hour. Not recommended for varnished surfaces.

CAUTION: EYE AND SKIN IRRITANT. In case of contact with eyes or skin, flush with water for at least 15 minutes. If irritation persists, seek medical attention. If swallowed, take large amounts of water. Do not induce vomiting. Get medical attention.

KEEP OUT OF REACH OF CHILDREN.

	TECHNICAL DATA	KRK-22
	KRUD KUTTER® ADHESIVE REMOVER	

PHYSICAL PROPERTIES

		ADHESIVE REMOVER
Composition		Proprietary Blend of Biodegradable Surfactants, Detergents and Emulsifiers
Solvents		Water
Weight	Per Gallon	8.42 lbs.
	Per Liter	1.01 kg
Color		Light Yellow
Clarity		Clear Liquid
Odor		Mild
pH (Concentrate)		12-13
VOC (Weight %)		5.0%
Practical Coverage		Varies with type and porosity of surface
Shelf Life		NA
Flash Point		>200°F (93°C)
Caution!		CAUTION: EYE AND SKIN IRRITANT. In case of contact with eyes or skin, flush with water for at least 15 minutes. If irritation persists, seek medical attention. If swallowed, take large amounts of water. Do not induce vomiting. Get medical attention. KEEP OUT OF REACH OF CHILDREN.
Safety Information		For additional information, see SDS

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.



Rust-Oleum Corporation
11 Hawthorn Parkway
Vernon Hills, Illinois 60061

Phone: 877-385-8155
www.rustoleum.com

Form: GDH-541
Rev.: 050925