

# HOM215CP

Mini circuit breaker, Homeline, 15A, 2 pole,  
120/240VAC, 10kA AIR, standard type, plug in,  
UL



## Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	15 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Short Circuit Current Rating	10 kA
Number of Spaces	2
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Clamp terminal for 2 cables
Wire Size	AWG 14...AWG 8 aluminium/copper)1 AWG 14...AWG 10 copper)2
Type of Packing	Consumer packaging

## Complementary

Tightening torque	35.40 Lbf.in (4.0 N.m) 0.00...0.02 in <sup>2</sup> (2.5... 10 mm <sup>2</sup> ) (AWG 16...AWG 14) 35.40 lbf.in (4.0 N.m) 0.01...0.03 in <sup>2</sup> (4...20 mm <sup>2</sup> ) (AWG 12...AWG 4)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

## Environment

Ambient Air Temperature for Operation	104 °F (40 °C)
---------------------------------------	----------------

## Ordering and shipping details

Category	01346-HOM 2 POL BULK BRKR 15-60A
Discount Schedule	CPH
GTIN	047569062759
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.00 in (7.62 cm)
Package 1 Weight	10.40 oz (294.835 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1800
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)

Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1270.00 lb(US) (576.062 kg)
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Height	3.20 in (8.128 cm)
Package 3 Width	3.00 in (7.62 cm)
Package 3 Length	10.20 in (25.908 cm)
Package 3 Weight	3.46 lb(US) (1.569 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	Lifetime
----------	----------