

ARVIN

PTL3520-PBR

Made in India, Arvin introduces textural depth and warmth to a classic lamp form. There's a noticeable play of light and shadow across the ridged surface of the domed base, creating movement and dimension. Patina Brass fittings and an off-white linen shade complement the earthy lamp base. The inviting nature of Arvin makes it the perfect accent piece in coastal, transitional, or bohemian interiors.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 20"

Width/Diameter: 19"

Canopy/Backplate: 9.25"

Product Weight: 5.51lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: Off White Linen

Shade 1 Top Width: 6"

Shade 1 Bottom L/W: 0" / 19"

Shade 1 Height: 9"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 96"

Cord Type: SPT-2 BLACK FABRIC

Switch Type: ON/OFF SWITCH ON SOCKET

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 22" x 22" x 18"

Carton 1 Weight: 9lb

Shipping Method: Ground

Country of Origin: IN

