



PIP® EZ-Twist™

Disposable Soft Polyurethane Foam Coded Ear Plugs - NRR 30 / SNR 38

- Just Insert & Twist! The fastest fitting foam ear plugs
- Shape conforms to most ear canals
- Softest most comfortable cylinder shaped ear plug
- Black PVC cord for convenience and to prevent loss of ear plugs
- NRR 30 protection

Applications

- Construction Applications
- Manufacturing
- Workshops
- Energy

Technical Data

Color	Orange
Sizes Available	OS
Packaging	Boxed
Packed	10 Boxes/Case
Case Dimensions (in)	21.37 x 16.38 x 9.62
Case Weight (lbs)	12.48
Country of Origin	Mexico
Hearing Style	Corded
Ear Plug Material	Polyurethane Foam
Shape	Barrel Push-In
Cord Material	PVC
Box Count	100
EN 352	EN352-2: Earplugs
Certifications	TAA Compliant

Performance Data

NRR Rating (ANSI S3.19-1974)	30
SNR Rating	38
SLC 80	25
SLC 80 Class	Class 4
Attenuation - High Frequency	38
Attenuation - Medium Frequency	34
Attenuation - Low Frequency	36

Care Instructions

These ear plugs are disposable, but when not in use should be kept in clean, dry condition.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
267-HPF610C	Orange	OS	616314268700		02616314268708