

Material and Ribbon Compatibility

B-# Material		M71-R4300 (Black)	M71-R6000 (Black)	M71-R6200 (Black)	M71-R6400 (Black)	M71-R6600 (Black)	M71-R4400-WT (White)	M71-R6800-WT (White)	M71-R6900 (Colors)
B-109	Polyethylene tags	●		▲					
B-145	Polyethylene tags		●	▲			▲		
B-145FR	Polyethylene tags		●	▲			▲		▲
B-321*	Polyolefin			●					
B-342	Polyolefin	●				▲			
B-344	Fluid-resistant polyolefin		▲			●			
B-345*	High-temp polyolefin		▲			●		▲	
B-351	Destructible vinyl		▲	●					▲
B-362	Destructible vinyl		●						▲
B-353*	Paper	●							
B-390*	Durasleeve polypropylene		●						▲
B-403	Dissolvable paper	●							
B-412	Polypropylene tags	▲		●					
B-422	Polyester		● UL						▲
B-423	Polyester		● UL	▲					▲
B-424	Paper	●							▲
B-425	Polypropylene	●		▲					
B-427	Vinyl	● UL		▲					
B-428	Polyester	● UL		▲					
B-430	Polyester		● UL	▲			▲		▲
B-432*	Polyester		● UL				▲		▲
B-433*	Polyester		● UL				▲		▲
B-435*	Polyester		● UL				▲		▲
B-437	Polyvinylfluoride	●							
B-439*	Vinyl		●	▲			▲		▲
B-459	Polyester		● UL						
B-472	Polyimide	●		▲					
B-473	Polyester		● UL						
B-483	Polyester		● UL						▲
B-486	Polyester	● UL		▲					
B-488	Polyester	● UL		▲					
B-489	Polyester	● UL		▲					
B-495*	Polyethylene naphthalate		● UL				▲		▲
B-498	Vinyl cloth	▲	▲	●					
B-499	Nylon cloth	● UL	▲	▲					▲
B-529	Polypropylene		●						▲
B-530	Tamper-resistant vinyl		●						▲
B-581	Vinyl		●						▲
B-582	Phosphorescent		●				▲		▲
B-584	Reflective		●				▲		▲
B-593	Polyester		●				▲		▲
B-595	Vinyl		●				▲		▲
B-717	Polyimide		● UL						
B-718	Polyimide		● UL						
B-719*	Polyimide		● UL						
B-724	Polyimide	●							
B-727	Polyimide		● UL						
B-854	ToughWash® metal detectable		●						
B-855	ToughWash® material		●						
B-7531*	Metallized polyester	●							
B-7536*	Polyester			●					
B-7546*	Void footprint polyester		● UL				▲		▲
B-7551*	Polyester			●					
B-7566*	Void footprint polyester		●				▲		▲
B-7576*	Void footprint polyester	● UL					▲		▲
B-7593*	Polyethelene		●				▲		▲
B-7596*	Vinyl			●					
B-7597*	Polyethelene	●							
B-7599*	Polyethelene tag	●							
B-7641	Low-smoke zero-halogen polyolefin		▲			●			
B-7643*	Thermoplastic polyether polyurethane	●				▲		▲	
B-7696*	Vinyl tag		●				▲		▲
B-8425*	Polypropylene		● UL						▲

View BradyID.com/techdata for TDS sheets on ribbon performance specifications.
 *This BMP®61 material also works in the BMP71 printer with media adapter.

● Recommended ribbon ▲ Acceptable ribbon
 UL These materials are UL recognized with its respective ribbon.

Pre-Printed Labels

BradyID.com/s36

Conduit and Voltage Labels

- Orange markers meet ASME (ANSI) Standard ZG3.22 and alert employees to potentially dangerous machinery or energized equipment
- Cards sold individually



Legend	Style A	Style B	Style C
(blank)	44099	44100	-
110 Volts	44101	44201	44301
115 Volts	44102	44202	44302
120 Volts	44104	44204	44304
120/208 Volts	44159	44259	44359
208 Volts	44106	44206	44306
220 Volts	44107	44207	44307
230 Volts	44108	44208	44308
240 Volts	44110	44210	44310
250 Volts	44111	44211	44311
277 Volts	44112	44212	-
277/480 Volts	44160	44260	44360
440 Volts	44113	44213	44313
460 Volts	44114	44214	44314
480 Volts	44115	44215	44315
550 Volts	44116	44216	-
600 Volts	44118	44218	-
2300 Volts	44134	44234	-
2400 Volts	44121	44221	-
4160 Volts	44122	44222	-

Legend	Style A	Style B	Style C
4800 Volts	44124	-	-
6900 Volts	44125	-	-
7200 Volts	44126	-	-
13,200 Volts	44151	-	-
AC	44127	44227	44327
Air Conditioning	-	44247	44347
Circuit #	44155	44255	-
Circuit Breaker	44157	44257	-
DC	44138	44238	44338
Electric Out of Service	-	44250	-
Emergency Service	-	-	44328
Fuse Box	44158	44258	-
Heating Circuit	-	44248	-
Light and Power	-	44242	44342
Lights	44133	44233	44333
On/Off	-	44256	-
Power	44132	44232	44332
Single Phase	44129	44229	44329
Three Phase	44131	44231	44331
Volts	44149	-	-

120 VOLTS

Style A:

(1) 2.25 in. x 9 in. marker per card

120 VOLTS 120 VOLTS

Style B:

(4) 1.125 in. x 4.125 in. markers per card

120 VOLTS 021

Style C:

(18) 0.5 in. x 2.25 in. markers per card

Pre-Printed Labels



Warning Labels

- Call attention to hazards on paperwork, equipment and packages
- Made of B-946 pressure sensitive vinyl
- **0.5, 1 and 2 inch labels:** 10 per card, 10 cards per pack
- **4 inch labels:** 3 per card, 10 cards per pack
- **8 inch labels:** 1 per card, 10 cards per pack



No Smoking

60237 2 in. x 2 in. Vinyl 50/pk.

* 5 labels per card. 10 cards per pack



Acid

60184 0.5 in. x 0.5 in. Vinyl 100/pk.

60195 1 in. x 1 in. Vinyl 100/pk.

60206 2 in. x 2 in. Vinyl 100/pk.

60217 4 in. x 4 in. Vinyl 30/pk.

60228 8 in. x 8 in. Vinyl 10/pk.



Battery Hazard

60186 0.5 in. x 0.5 in. Vinyl 100/pk.

60197 1 in. x 1 in. Vinyl 100/pk.

60208 2 in. x 2 in. Vinyl 100/pk.

60219 4 in. x 4 in. Vinyl 30/pk.

60230 8 in. x 8 in. Vinyl 10/pk.



Electrical Voltage

60235 0.5 in. x 0.5 in. Vinyl 100/pk.

60191 1 in. x 1 in. Vinyl 100/pk.

60202 2 in. x 2 in. Vinyl 100/pk.

60213 4 in. x 4 in. Vinyl 30/pk.

60224 8 in. x 8 in. Vinyl 10/pk.



Explosive Atmosphere

60189 0.5 in. x 0.5 in. Vinyl 100/pk.

60200 1 in. x 1 in. Vinyl 100/pk.

60211 2 in. x 2 in. Vinyl 100/pk.

60222 4 in. x 4 in. Vinyl 30/pk.

60233 8 in. x 8 in. Vinyl 10/pk.



Explosive Material

60182 0.5 in. x 0.5 in. Vinyl 100/pk.

60193 1 in. x 1 in. Vinyl 100/pk.

60204 2 in. x 2 in. Vinyl 100/pk.

60215 4 in. x 4 in. Vinyl 30/pk.

60226 8 in. x 8 in. Vinyl 10/pk.



Flammable Material

60181 0.5 in. x 0.5 in. Vinyl 100/pk.

60192 1 in. x 1 in. Vinyl 100/pk.

60203 2 in. x 2 in. Vinyl 100/pk.

60214 4 in. x 4 in. Vinyl 30/pk.

60225 8 in. x 8 in. Vinyl 10/pk.



Hazardous Area

60188 0.5 in. x 0.5 in. Vinyl 100/pk.

60199 1 in. x 1 in. Vinyl 100/pk.

60210 2 in. x 2 in. Vinyl 100/pk.

60221 4 in. x 4 in. Vinyl 30/pk.

60232 8 in. x 8 in. Vinyl 10/pk.



Laser Beam

60187 0.5 in. x 0.5 in. Vinyl 100/pk.

60198 1 in. x 1 in. Vinyl 100/pk.

60209 2 in. x 2 in. Vinyl 100/pk.

60220 4 in. x 4 in. Vinyl 30/pk.

60231 8 in. x 8 in. Vinyl 10/pk.



Radioactive Material

60185 0.5 in. x 0.5 in. Vinyl 100/pk.

60196 1 in. x 1 in. Vinyl 100/pk.

60207 2 in. x 2 in. Vinyl 100/pk.

60218 4 in. x 4 in. Vinyl 30/pk.

60229 8 in. x 8 in. Vinyl 10/pk.



Static Sensitive Devices

60190 0.5 in. x 0.5 in. Vinyl 100/pk.

60201 1 in. x 1 in. Vinyl 100/pk.

60212 2 in. x 2 in. Vinyl 100/pk.

60223 4 in. x 4 in. Vinyl 30/pk.

60234 8 in. x 8 in. Vinyl 10/pk.



Toxic Material

60183 0.5 in. x 0.5 in. Vinyl 100/pk.

60194 1 in. x 1 in. Vinyl 100/pk.

60205 2 in. x 2 in. Vinyl 100/pk.

60216 4 in. x 4 in. Vinyl 30/pk.

60227 8 in. x 8 in. Vinyl 10/pk.