Aragon | E11203-WAGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Featuring carved Spanish Alabaster shades in sleek cylindrical forms, the Aragon collection conceals high-powered LED light sources within, providing both beauty and functionality. The natural alabaster is elegantly complemented by plated Gold accents, adding an upscale, luxurious touch. Available as pendants or sconces, these fixtures are damp rated, making them ideal for interior spaces including bathrooms.



MEASUREMENTS

DIMENSION	: 5" W x 25.75" H x 3.5" Ext
MAX OAH	: 5" W x 14.5" H
HANGING WEIGHT	: 3.5 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,700 Rated (1,500 Del.)
BULB	: 3 x 9W LED DC Integrated , 27W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

White Alabaster / Gold (WAGLD)

MATERIAL

Alabaster, Aluminum

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Vertical/Horizo
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com