

QOT2020CP

Tandem mini circuit breaker, QO, 2 x 1 pole at 20A, 120/240VAC, 10kA, plug in mount, consumer pack



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Circuit Breaker Type	Tandem
Ratings	HACR rated
Electrical Connection	Pressure plate
Type of Packing	Consumer packaging

Complementary

Interrupt Rating	10 kA 120/240 V AC 50/60 Hz
Number of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper AWG 12...AWG 8 aluminium
Tightening Torque	44.25 lbf.in (5 N.m) 0.02...0.04 in ² (10...25 mm ²) (AWG 8...AWG 2)
Height	3.23 in (82 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.33 lb(US) (0.150 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	01329-QO TANDEM BULK BRKRS.
Discount Schedule	CPQ
GTIN	047569008962
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.70 in (1.778 cm)
Package 1 Width	2.90 in (7.366 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	5.29 oz (150.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.90 in (9.906 cm)

Package 2 Width	2.90 in (7.366 cm)
Package 2 Length	7.70 in (19.558 cm)
Package 2 Weight	3.44 lb(US) (1.56 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	8.30 in (21.082 cm)
Package 3 Width	8.20 in (20.828 cm)
Package 3 Length	19.70 in (50.038 cm)
Package 3 Weight	35.15 lb(US) (15.944 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Halogen content performance	Halogen free product