

Product Specifications



#10 x 3/4" Slotted Hex Washer High Head Metal Piercing Screw (5500pc Tuff Pail)

Part Number SP1034TP5500HH

UPC 781002860990

High Head Sharpeez Screws are engineered with an exceptionally sharp point designed to easily pierce thin sheet metal and create their own mating threads with precision. Featuring a heightened hex head for extra grip and superior resistance to stripping, Sharpeez Screws deliver fast, reliable fastening performance. Ideal for sheet metal applications, they are widely used in HVAC installations and other demanding metal-to-metal tasks.



Physical Characteristics

Type	Sharpeez Screw
Style	High Head
Drive Type	Slotted
Head Type	Hex Washer
Thread Type	DWF
Point Type	Sharp
Size	#10 x 3/4"
Dia./Thread Size	#10
Hex Size	5/16"
Length (in)	3/4"
Head Height	0.170" - 0.157"
Thread Pitch\Thread Per Inch	15
Drive Size	#2
Material	Carbon Steel
Finish	Zinc Plated

Performance Data

Special Features	Ultra-sharp piercing point, Double-lead speed thread, Non-walking piercing point, Ideal for sheet metal, Zinc-plated finish
Applications	Sheet Metal and HVAC

Packaging Details

Standard Qty	5500
Price Per	100
Package Length	9.45
Package Width	7.68
Package Height	9.84
Package Weight	40.81

Certifications

UNSPSC	31161506
RoHS Compliant	Yes