SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

62-1205 - LED Landscape Flood 9W; Bronze Finish; 3000K

WET LOCATION | FC | RoHS COMPLIANT | 50,000 HOURS | 60° BEAM | 120 VOLT

GENERAL

Company	NUVO
EA Height	3.54
EA Width	3.62
EA Length	6.57
Bulb Included	Integrated
Diameter	2.63
Material	Die-cast Aluminum
Fixture Type	Flood Light
Status	Active
Style	Modern and Contemporary
CCT Selectable	No
Wattage Selectable	No
Finish Family	Bronze
Amps	0.075A
Has Camera	No
IOT Enabled	No
Photo Cell	No Photocell
SDS Class	LED_Fixture
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	75W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K
Dimmable	Non-Dimmable
Hours Rated	50000
Beam Angle (degree)	60
Color Temp	Warm White
CRI	80+
Operating Frequency	60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	900L
Volts	120v
Watts	9W
Connection	Direct Wired

PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	PAR20
Mounting Procedure	Pole/Post/Plate

ADDITIONAL INFO

Warranty	5-Years

PACKAGING

UPC	045923680175
Case Cube	0.6538
Case Height	7.68
Case Length	21.73
Case Quantity	12
Case UPC	10045923680172
Case Weight	11.03
Case Width	6.77
EA Cube	0.0487
EA Height	3.54
EA Length	6.57
EA Quantity	1
EA Weight	0.84
EA Width	3.62
Pack Type	Box
Web Height	4.0
Web Length	6.25
Web Width	2.63

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
UL Application	Landscape
DLC Approved	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026