



Technical Data

Color	White
Sizes Available	L-XL
Packaging	Bagged Pair
Packed	15 Pair/Case
Case Dimensions (in)	22.44 x 14.96 x 9.84
Case Weight (lbs)	20.06
Country of Origin	Japan
Polymer	Silicone
Grip	Smooth
Cuff	Open
Length	15"
Construction	Supported
Certifications	TAA Compliant

Performance Data

ISO Cleanroom	ISO 5 (Class 100)
Temperature Resistant	Extreme Cold

QRP® Qualatherm®

Heat & Cold Resistant Glove with Silicone Rubber Outer Shell and Nylon Lining - 15"

- Packaged for Class 100 (ISO5/M3.5) applications
- Wet or dry contact temperatures from -78F to 392F (-61.4C to 200C)
- PolyTuff silicone elastomer is sulfur-free. Excellent resistance to chemicals, solder and fluxes
- RoHS Compliant

Care Instructions



Machine Wash



Water Temp 40°C



Do Not Bleach



Hang Dry

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
74GL	White	L	616314280368	10616314280365	20616314280362
74GXL	White	XL	616314280375	10616314280372	20616314280379