

Strong and robust unlined welding and heat-resistant glove in premium goatskin.

TEGERA® WELDING 118A

Learn more

WITHSTANDS WELDING SPARKS AND SPLASH

Strong and robust unlined welding and heat-resistant glove in full grain goatskin and split cowhide. Withstands welding sparks, grinding splash, and contact heat up to 100°/212°F. Reinforced KEVLAR® seams and index finger. Perfect for welding work.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Good fit

FUNCTIONS

- Withstands contact heat up to 100°C
- Reinforced index finger
- Reinforced seams
- Withstands welding sparks and grinding splash

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Burn injuries, Heat injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

All-year use, Warm environments, Dirty environments, Harsh environments

PRIMARY AREAS OF USE

Engineering, Metalwork, Welding, Hot work, Mining

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Oil and gas extraction, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Mining and quarrying

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Heat protection gloves, Welding gloves
CATEGORY Cat. III
COLLECTION Welding
PALM MATERIAL Full grain goatskin
BACK MATERIAL Split cowhide
LINING Unlined
LENGTH 310-360 mm
DEXTERITY 5
COLOUR Yellow
PAIRS PER: BUNDLE/CARTON 12/60
DISPLAY TYPE Thread
FASTENING Elasticated 180°
CUFF STYLE Safety cuff
CUFF MATERIAL Leather
OUTER MATERIAL SPECIFICATION Leather

COMPLIANCE

CE 2777

UKCA 0321

EAC

TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018
3121X

EN 407:2020
412X4X

EN 12477:2001+A1:2005

Type B

EN 1149-2:1997
$R > 1,0 \times 10^5\ \Omega$

ANSI 3 ABR

SIZE		ARTICLE NUMBER	EAN
7	S	118A-7	7340118312781
8	M	118A-8	7340118312804
9	L	118A-9	7340118312828
10	XL	118A-10	7340118312729
11	XXL	118A-11	7340118312743
12	3XL	118A-12	7340118312767

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.