

ISAAC

B4204-BRZ

The industrial-inspired Isaac features an elongated, tubular head and thoughtfully designed hardware details. With integrated LED and three pivot points, this picture light ensures both high efficiency and adjustability. The slim silhouette enhances a space without distracting from your artwork. Isaac is available in two sizes and two finishes, Patina Brass and Bronze.

FINISHES

BRONZE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 3.25"

Width/Diameter: 24"

Canopy/Backplate: 5.5"

Product Weight: 2.86lb

Extension: 8.5"

Top to Center: 1.25"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 14

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: ELV, TRIAC

Gem Box Required (2"x3"): Yes

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 375

Title 24: No

Field Serviceable: No

SHIPPING

Carton 1: 28" x 12" x 7"

Carton 1 Weight: 5lb

Shipping Method: Ground

Country of Origin: VN

