



TEGERA® 17

Learn more

QUALITY GLOVE AGAINST HEAT

Long-lasting protection against heat for heavy-duty jobs. All day comfort thanks to the flexible split cowhide. Cotton jersey liner inside the glove for better sweat management. Reinforced seams for extra durability. Elasticated wrist for better fit.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Very durable
- Good fit

FUNCTIONS

- Withstands contact heat up to 100°C
- Reinforced seams
- Flame retardant
- Withstands welding sparks and grinding splash

LEATHER WORKING GROUP

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Burn injuries, Heat injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Warm environments, Harsh environments

PRIMARY AREAS OF USE

Engineering, Metalwork, Mining

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Mining and quarrying

TYPE OF WORK

Heavy weight

SPECIFICATION

TYPE All-round work gloves, Heat protection gloves, Heavy duty gloves
CATEGORY Cat. III
PALM MATERIAL Split cowhide of top quality
BACK MATERIAL Split cowhide of top quality
LINING Fully lined
LINING MATERIAL Cotton, Jersey
LENGTH 240-280 mm
DEXTERITY 2
COLOUR Yellow
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Thread
FASTENING Elasticated 180°
CUFF STYLE Safety cuff
CUFF MATERIAL Leather
INNER MATERIAL SPECIFICATION Cotton, Polyester
OUTER MATERIAL SPECIFICATION Leather

COMPLIANCE

CE 2777

UKCA Cat. III

EAC

TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 3233X

EN 407:2020 4132XX

ANSI 4 ABR

SIZE		ARTICLE NUMBER	EAN
8	M	17-8	7392626001787
9	L	17-9	7340118300818
10	XL	17-10	7392626001794
11	XXL	17-11	7392626027459
12	3XL	17-12	7340118300993

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.