5Seconds™
Material Handling and More...

Tyson-850

Pallet Jack with Scale & Printer

6600 LBS, 48” x 27”

SKU: 555006



Description

The 5Seconds Tyson-850 Hand Pallet Jack with Scale & Printer combines powerful material handling with precise weighing and on-demand printing, allowing operators to lift, move, weigh, and print weight tickets in one smooth operation. With a 6,600 LBS load capacity and 48" × 27" tapered forks, it easily handles standard pallet loads in warehouses, shipping docks, and logistics operations. The integrated digital scale provides weighing accuracy of ±1.1 lbs on a high-visibility LED display, while the built-in printer instantly produces weight tickets for improved inventory tracking and shipping documentation. Built with heavy-duty steel construction, a durable powder coat finish, a reliable BF hydraulic pump, polyurethane steering and load wheels, and an ergonomic loop handle, the Tyson-850 delivers smooth performance, long-lasting durability, and operator comfort shift after shift.

Product Features

- 6,600 LBS load capacity
- Built-in digital scale
- BF Hydraulic Pump
- 48" x 27" fork size
- Ergonomic rubber handle
- Single polyurethane load wheel
- Polyurethane steering wheels
- Heavy-duty steel construction

SKU	Item Description	Capacity	Size	Weight	Height
555006	Pallet Jack with Scale & Printer	6600 LBS	48" x 27"	209.44 lbs	48"

Specifications


SKU: 555006

	FEATURE	DETAILS
1	Load capacity	6600 LBS
2	Lowered Fork Height	0.79"
3	Lift Height	3.54"
4	Steering wheel	7.09"
5	Loading Wheels	2.75"
6	Overall Width of Forks	27"
7	Fork Length	48"
8	Battery	6V 4.5Ah
9	Wheel Type	PU
10	Service Weight	209.44 lbs
11	Weighing Accuracy	1.1 lbs
12	Plate Thickness	4.5mm

Printer Parameters

CODE	DESCRIPTION	VALUE RANGE	REMARKS
dF=xx	Stability threshold	00~99	Actual value=df×division(d)
stA=xx	Stability sampling count	00~99	10 samples per second
dy=x	Auto print switch	0=Disable,1=Enable	
PCod=x	Print format	0=Simple print;1=Standard print;2=Simple(no time);3=Label print;4=Template printer	
PrL=x	Paper feed length	00~99	
Prn=x	Print copies	1~5	Valid for Standard & Label format only
PLxxxx	Minimum print weight	2~5000	
PS=X	Print permission restriction	0=No limit;1=Zero required before print;2=Zero + stable reading required	

Dimensions


47.24″
23.62″
48″
3.54″
2.75″
2.75″
0.79″
2.75″
Ø7.09″
D
6.3″
14.17″
Inside
27″
R1350
102°
102°
6.3″

Product Structure



Application Image

