Geist | E25190-TW

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Geist reimagines 20th-century plasterwork in a sculptural ring crafted from artisan plaster. Integrated LEDs provide both uplight and downlight, creating an atmospheric glow. Available in a striking Black plaster finish as well as the classic White, Geist blends sculpture with modern LED lighting technology for minimalist and elevated spaces alike.



MEASUREMENTS

DIMENSION	: 10" L x 10" W x 5" H x 4" Ext
MAX OAH	: 5" W x 3.5" H
HANGING WEIGHT	: 3.5 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 960 Rated (750 Del.)
BULB	: 2 x 6W LED PCB Integrated , 12W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: TriacÂ orÂ ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Up

FINISHES OPTION

Black (BK)

Textured White (TW)

MATERIAL

Gypsum, Steel

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up
RATED LIFE 30000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com