PRODUCT INFORMATION PACKET

Model No: H940V1
Catalog No: H940V1
General Purpose Motor, 1/2 HP, 3 Ph, 60 Hz, 575 V, 1800 RPM, J56 Frame, DP



Regal and Century are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications

Output HP	1/2 Hp	Output KW	0.37 kW
Frequency	60 Hz	Voltage	575 V
Current	.70 A	Speed	1725 rpm
Service Factor	1.25	Phase	3
Duty	Continuous	Insulation Class	B
Frame	J56	Enclosure	Drip Proof
Thermal Protection	Thermally Protected	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	Number of Speeds	1

Technical Specifications

Electrical Type	Polyphase, Induction Type, Single Or Dual Voltage	Starting Method	Across The Line
Poles	4	Rotation	Reversible Counterclockwise
Mounting	Cushion Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	11.07 in
Frame Length	5.13 in	Shaft Diameter	0.625 in
Shaft Extension	1.94 in		
Outline Drawing	H940V1-S01	Connection Drawing	17050814.PCX

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/29/2022