



QRP® PolyTuff®

Polyurethane Electrostatic Dissipative (ESD)
Glove - 8 mil

- Packaged for ISO 5 (Class 100) applications
- Tough, sheer PolyTuff polyurethane (8 mil) film affords a high degree of tactile sensitivity
- Static dissipative 10(6) ohms
- Sulfur free, no carbon shedding
- Ergonomic Comfort Curve hand specific design
- ESD safe compliance to ANSI/ESD S20.20-2014
- Compliant with ASTM and IEST-RP-CC005.4 standards
- For use with Class I and Class II static sensitive devices
- RoHS Compliant



Technical Data

Color	Black
Sizes Available	S-XL
Packaging	Case
Packed	5 Bags/Case
Case Dimensions (in)	17.00 x 8.00 x 5.00
Case Weight (lbs)	2.85
Country of Origin	Japan
Polymer	Polyurethane
Grip	Smooth
Cuff	Straight
Length	12"
Powder	Powder Free
Thickness	8 Mil
Construction	Unsupported, ESD Safe
Certifications	TAA Compliant

Performance Data

ISO Cleanroom	ISO 5 (Class 100)
Static Control Property	Static Dissipative

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
28GS	Black	S	616314278068	10616314278065	20616314278062
28GM	Black	M	616314278051	10616314278058	20616314278055
28GL	Black	L	616314278044	10616314278041	20616314278048
28GXL	Black	XL	616314278075	10616314278072	20616314278079