
Hover | E21375-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Minimalist batons of extruded Black aluminum are fitted with V shaped acrylic diffusers for a wider beam of light. They can be arranged in numerous configurations allowing creativity and design of your own unique sculpture.



*max overall height

MEASUREMENTS

DIMENSION	: 47.5" L x 47.5" W x 17.25" H
MAX OAH	: 123.25" OAH
CANOPY	: 17.25" W x 1.75" H x 17.25" L
HANGING WEIGHT	: 13 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 6,720 Rated (4,320 Del.)
BULB	: 5 x 18W LED PCB Integrated , 96W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: ELV or Triac CL
CRI	: 80 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum, Steel, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 90
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com