

GLADDEN

B5720-TBK/PBR

The lantern-inspired silhouette of Gladden emphasizes clean lines and purposeful design. A Textured Black frame is accented by Patina Brass ball details, giving it an old-world character. The rippled texture of the heavy seeded glass softens the light housed within the frame. Gladden is well-suited for the outdoors, but it can also be adapted for indoor use. Available in two sizes with a Dark Sky rating.

FINISHES

TEXTURE BLACK w/ PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 20.25"

Width/Diameter: 11.5"

Canopy/Backplate: 5.5"

Product Weight: 8lb

Extension: 9"

Top to Center: 4.5"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear Seeded

Shade 1 Top Width: 10"

Shade 1 Bottom L/W: 0" / 8"

Shade 1 Height: 11"

Shade 2: Glass

Shade 2 Finish: Clear Seeded

Shade 2 Top Width: 5.5"

Shade 2 Bottom L/W: 0" / 4.75"

Shade 2 Height: 11"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: Yes

SHIPPING

Carton 1: 58" x 35" x 32"

Carton 1 Weight: 11lb

Shipping Method: Truck Only

Country of Origin: VN

